

Scotseal family interchanges



Scotseal family

Scotseal PlusXL	Scotseal Classic	National	National 5 Star	Stemco Guard. / G.G.* wheel sets	Stemco (seal w/ring)	Stemco Voyager	Stemco Discover
23590	---	370199A	---	---	---	383-0175	---
28759	28758	370150A	---	308-0866	(2164/1008)	383-0166	---
29400	---	370211A	---	---	---	383-0176	---
34384	34387	370047A	---	309-0935/ 392-9035	(2728/1728) (2057/1062)	---	---
34971	34975	370132A	---	308-0863/ 382-8063	(2721/1721) (2133/1036)	---	---
34994	35000	370169A	---	392-9036/ 392-9111	(2057/1063)	---	---
35058	35066	370001A	380001A	308-0836/ 382-8036	(2702/1702) (2036/1036)	383-0136	383-0236
---	36358/ 36365	370011A	---	382-8071	(2216/1034)	383-0171	---
---	38750	370024A	---	309-0915/ 392-9099	(2102/1501)	393-0115	---
38776	38780	370023A	380023A	309-0912/ 392-9099	(2707/1707) (2102/1501)	393-0112	393-0212
39426♦	---	---	---	---	---	---	---
39979 w/456301	39988 w/456301	370033A/ w/AR-12	---	382-8039/ 382-8023	(2039/1038) (2039/1011)	383-0139	383-0239
40091	40086	370066A	---	382-8001	(2086/1013)	383-0101	---
40129	40136	370349A/ 370036A	380036A	307-0713/ 372-7098	(2704/1704) (2109/1507) (2109/1013)	373-0113	373-0213
42627	42623	370065A/ 376590A	380065A/ 386590A	307-0723/ 372-7099	(2705/1705) (2023/1503)	373-0123	373-0223
42673	42672	370031A	380031A	309-0904/ 392-9112/ 392-9130	(2718/1705) (2132/1515)	393-0104	393-0204
43754	43752	370338A/ 370037A	---	307-0744/ 372-7095	(2709/1709) (2118/1510)	373-0144	---
43761	43764	370182A/ 370048A	380048A	308-0864/ 382-8064	(2711/1711) (2137/1037)	383-0164	383-0264
---	43860	370019A	---	309-0965/ 392-9096	(2713/1713) (2114/1508)	---	---
44916	44922	370124A	---	308-0853/ 382-8053	(2708/1708)	383-0153	---
---	44964/ 45010	370178A	---	392-9033	---	---	---
45093	45099	370022A	380022A	309-0903/ 392-9094	(2706/1706) (2129/1511)	393-0103	393-0203
45095	45103	370131A	380131A	308-0855/ 308-0856/ 382-8056	(2710/1710) (2710/1706)	383-0156	---
45157	45160	370021A	---	309-0964/ 392-9088	(2712/1712) (2113/1517)	---	---
46300	46305	370025A	380025A/ 386002A	307-0743/ 372-7097	(2701/1701) (2110/1504) (2110/1048)	373-0143	373-0243
47691**/ 47692	47697	370003A	380003A	309-0973/ 392-9131	(2703/1703) (2106/1502)	393-0173	393-0273
48002	48000	370005A/ 370173A	---	309-0960/ 392-9081	(2717/1761) (2009/1079)	---	---
---	48690	370195A	---	392-9054	---	393-0134	---

* Guard. (Guardian HP) / G.G. (Grit Guard)

** Narrow OE version

♦ Scotseal Plus design

Scotseal family popular applications

Scotseal PlusXL	Scotseal Classic	Axle	Application
23590	---	Front Axle	GMC, Isuzu (8,000#)
28759	28758	Front Axle	Arvin Meritor/Rockwell, Dexter, International, Spicer (6,000#; 7,500#)
29400	---	Front Axle	GMC, Isuzu (11,000#)
34384	34387	Drive Axle	Ford, Navistar, Arvin Meritor/Rockwell, Eaton
34971	34975	Front Axle	Ford, Arvin Meritor/Rockwell
34994	35000	Drive Axle	Eaton, Navistar
35058	35066	Front Axle	Ford, Navistar, Arvin Meritor/Rockwell, Kenworth, Peterbilt, Freightliner, Volvo-White (12,000#)
---	36358/36365	Front Axle	GMC, Mack
---	38750	Drive Axle	Eaton, GMC (incl. Chevrolet), Arvin Meritor/Rockwell, Dana, Spicer (17,000# single; 34,000# tandem)
38776	38780	Drive Axle	Ford, Navistar, Arvin Meritor/Rockwell, Eaton, Volvo-White (34,000#)
39426♦	---	Front Axle	Volvo-White
39979 w/456301	39988 w/456301	Front Axle	Mack (12,000#)
40091	40086	Front Axle	Arvin Meritor/Rockwell Transit
40129	40136	Trailer Axle	Dana Spicer, Arvin Meritor/Rockwell, Eaton, Standard Forge (19,000#)
42627	42623	Trailer Axle (Pro-Par)	Fruehauf, Arvin Meritor/Rockwell (TP Series)
42673	42672	Drive Axle	Mack (44,000#)
43754	43752	Trailer Axle	Arvin Meritor/Rockwell, Eaton (20,000#)
43761	43764	Front Axle	Ford, Navistar, Kenworth, Arvin Meritor/Rockwell, Volvo-White, Mack, GMC (16,000#)
---	43860	Drive Axle	Eaton, Ford, GMC, Navistar, Arvin Meritor/Rockwell, Volvo-White
44916	44922	Front Axle	Navistar
---	44964/45010	Drive Axle	GMC Coach, Arvin Meritor/Rockwell
45093	45099	Drive Axle	Mack (34,000#; 38,000#)
45095	45103	Front Axle	Navistar (9,000#)
45157	45160	Drive Axle	Eaton, Ford, GMC, Navistar, Mack, Arvin Meritor/Rockwell
46300	46305	Trailer Axle	Dana Spicer, Arvin Meritor/Rockwell, Eaton, Standard Forge (22,500#)
47691**/ 47692	47697	Drive Axle	Ford, Navistar, Arvin Meritor/Rockwell, Eaton, Kenworth, Peterbilt, Freightliner, Volvo-White (38,000#; 46,000#)
48002	48000	Drive Axle	Mack, GM
48690	---	Drive Axle	Meritor Transit

** Narrow OE version

♦ Scotseal Plus design



View detailed technical and product videos at www.skfpartsinfo.tv



Follow us on Twitter @skfpartsinfo to stay on top of all the latest technical and product information.

© SKF and Scotseal are registered trademarks of the SKF Group.

© SKF Group 2013

The contents of this publication are the copyright of the publisher and may not be reproduced (even extracts) unless permission is granted. Every care has been taken to ensure the accuracy of the information contained in this publication but no liability can be accepted for any loss or damage whether direct, indirect or consequential arising out of the use of the information contained herein.

Publication 457409 • rev. 11/14 Printed in U.S.A.

SKF VSM NA
890 N. State Street
Suite 200
Elgin, IL 60123
800-882-0008
www.vsm.skf.com

